

Substation - Aluminum Rigid Spacer

By Burndy
Catalog # [CPR46A4](#)



Al 2 Conductor Cable Spacer, 1200 -1600 kcmil AAC, 1113 - 1351.5 kcmil ACSR, 230 kV Max., Aluminum H/W.

Application

Substation

General

Catalog Number	CPR46A4
Connector Type	Spacer
Installation Torque Recommended in-lb	480 lb-in
Material	Aluminum Alloy, Cast
Material - Hardware	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810472538
UPC 12 Digit	7818104725388

Dimensions

Dimension - B Length inch	2.13 in
Dimension - Height inch	2.73 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	5.97 in
Dimension - Width inch	2.13 in
Dimension - Width mm	54 mm

Conductor Related

Conductor - ACSR Str Size Range	1113 kcmil-1351.5 kcmil
Conductor - AL Str Size	1200 kcmil;1250 kcmil;1272 kcmil;1300 kcmil;1351 kcmil;1400 kcmil;1431 kcmil;1500 kcmil;1590 kcmil;1600 kcmil
Conductor - AL Str Size Range	1200 kcmil-1600 kcmil
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section L - Bolted Substation](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_DFCPR_LineArt](#)
[Sales Drawings - 10025188](#)