



**CS3CI58220J, Medium Voltage
Cold Shrink Termination Kit, 5-8kV
3-Phase Conversion Series-Indoor,
Sleeve w/o Boot for Jacketed
Concentric Conductor**

By Burndy
Catalog # [CS3CI58220J](#)



The Type CS3CI58-J Series of 3 Phase Conversion Kits with Outdoor Sleeves without Boot for Jacketed Concentric Conductor. Conversion kits includes indoor cold shrinkable tube (unprinted), seal, cable tie, and installation guide. Conforms to IEEE-48-2009, Class 1 and ISO/IEC 17025 Standards. Test reports available upon request.

General

Boot Type	NO
Catalog Number	CS3CI58220J
Environmental Conditions	
Material	Caoutchouc de silicone
Pin Type	N/A
Series	UD-JC
Terminal Type	N/A
Type	
UPC	621945584990

Electrical Ratings

Phase	3-Phase
Voltage Rating	5/8 kV

Conductor Related

Conductor Range	5-8kV: #2 AWG-250 kcmil 15kV: #2-1 AWG
-----------------	--

Logistics

Carton Quantity	3
-----------------	---

Product Assets

- [Brochures - BURNDY_MVCS_CS3CI-J_CutSheet_CAN FR](#)
- [Brochures - BURNDY_MVCS_CS3CI-J_CutSheet_CAN EN](#)
- [Brochures - Cold Shrink Medium Voltage Cable Terminations Brochure](#)
- [Catalog Page - BURNDY_MVColdShrinkTerminationKits_CS3CI-J_CatCut](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section D - Shrink Tubing](#)
- [Sales Drawings - 50095782](#)



A proud member of the Hubbell Family.