



CSGO252810250, Cold Shrink Medium Voltage Termination Kit 25-28kV Outdoor

By Burndy
Catalog # [CSGO252810250](#)

Cold shrink cable terminations provide a quick, easy, safe and cost effective installation. No installation tools required, spiral rip cord design unwinds easily and enables quick removal of the hold-out core. Suitable for 25 to 28 kV Outdoor Industrial applications. Conforms to IEEE-48-1996, Class 1 and ISO/IEC 17025 Standards. Test reports available upon request.



General

Boot Type	NO
Catalog Number	CSGO252810250
Environmental Conditions	
Material	
Pin Type	N/A
Series	G
Terminal Type	N/A
Type	
UPC	621945584501

Electrical Ratings

Phase	1-Phase
Voltage Rating	25/28 kV

Conductor Related

Conductor Range	<ul style="list-style-type: none">5-8kV: 350-750 kcmil15kV: 4/0 AWG-500 kcmil25-28kV: 1/0 AWG-250 kcmil
-----------------	---

Logistics

Carton Quantity	1
Pallet Quantity	20

Product Assets

[Brochures - BURNDY_MVCS_CSGO_CutSheet_CAN EN](#)
[Brochures - BURNDY_MVCS_CSGO_CutSheet_CAN FR_01](#)
[Brochures - Cold Shrink Medium Voltage Cable Terminations Brochure](#)
[Catalog Page - BURNDY_MVColdShrinkTerminationKits_CSGO_CatCut](#)
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section D - Shrink Tubing](#)
[Sales Drawings - 50095762](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-CSGO252810250-SPEC-EN | REV 6/2024