



**CT110200SSBB0, Nylon Cable Tie,  
110 lb Tensile Strength, Stainless  
Steel Barb, 8.7" Long, Black**

By Burndy  
Catalog # [CT110200SSBB0](#)

Nylon Stainless Steel BARB Cable Ties, 8.7 IN L, .28 IN W,  
Tensile Strength: 110 Lbs,Installation Tool:MK9.



**General**

|                                       |              |
|---------------------------------------|--------------|
| Color                                 |              |
| Material                              | Nylon 6/6    |
| Rating - Minimum Tensile Strength lbs | 110 lb       |
| Trade Name                            | UNIRAP™      |
| UPC                                   | 781810565377 |

**Dimensions**

|                                      |         |
|--------------------------------------|---------|
| Dimension - Bundle Diameter Max inch | 2.01    |
| Dimension - L Length Overall mm      | 221 mm  |
| Dimension - Length Overall inch      | 8.7 in  |
| Dimension - Width inch               | 0.28 in |
| Dimension - Width mm                 | 7 mm    |

**Certifications And Compliance**

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Certification - cULus              | Y   |
| Standards - RoHS Compliance Status | CM  |

**Logistics**

|                 |      |
|-----------------|------|
| Carton Quantity | 5000 |
|-----------------|------|

**Product Assets**

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 30022708](#)



A proud member of the Hubbell Family.