



CT110200SSBC0, Nylon Cable Tie, 110 lb Tensile Strength, Stainless Steel Barb, 8.7" Long, Black

By Burndy
Catalog # [CT110200SSBC0](#)

Nylon Stainless Steel BARB Cable Ties, 8.7 IN L, .28 IN W, Tensile Strength: 110 Lbs,Material:Nylon 6/6.



General

Application	For use with self-locking stainless steel barb
Catalog Number	CT110200SSBC0
Color	Black
	Noir
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	110 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564776

Dimensions

Dimension - Bundle Diameter Max inch	2.01
Dimension - L Length Overall mm	221 mm
Dimension - Length Overall inch	8.70 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000
-----------------	------

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30022708](#)



A Hubbell brand