



CT110325SSBC, Nylon Cable Tie, 110 lb Tensile Strength, Stainless Steel Barb, 3.15" Bundle, Natural

By Burndy
Catalog # [CT110325SSBC](#)

Nylon 6/6 Cable Tie with Stainless steel Barb, 110 Lbs, Natural, 3.15" Bundle Dia., Package: 100.



Application

For use with self-locking stainless steel barb

General

Catalog Number	CT110325SSBC
Color	
EU RoHS Indicator	Yes
Rating - Minimum Tensile Strength lbs	110 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564783

Dimensions

Dimension - Bundle Diameter Max inch	3.15
Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.81 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000
-----------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section G - Wire Management](#)
[Sales Drawings - 30022708](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-CT110325SSBC-SPEC-EN | REV 6/2024