



CT175600Q0, Cable Tie, 175 Lb Tensile, UV Black

By Burndy
Catalog # [CT175600Q0](#)



Nylon 6/6 Standard Cable Tie, UV Black, 175 Lbs Min Ten Strgth,
21.00" L, 0.35" W.

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

Application

For Outdoor Applications

General

Catalog Number	CT175600Q0
Color	UV Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	0 °C
Rating - Minimum Tensile Strength lbs	175
Sub Brand	UNIRAP,CABLE TIE
Tool Type	Heavy
Trade Name	UNIRAP™
Type	Heavy
UPC	781810334119
UPC 14 Digit GTIN	00781810334119

Dimensions

Dimension - Bundle Diameter Max inch	7
Dimension - L Length Overall mm	622 mm

Dimension - Length Overall inch	24.51 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	Yes
Certification - cULus	No
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-10-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	500
-----------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) -
BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)
[Specifications - CT175600Q0 Specification Sheet English](#)
[Specifications - CT175600Q0 Specification Sheet French](#)



A Hubbell brand