



CT40137SSBC, Nylon Cable Tie, 40 lb Tensile Strength, Stainless Steel Barb, 5.91" Long, Natural

By Burndy
Catalog # [CT40137SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 5.91 IN L, .14 IN W, Tensile Strength: 40 Lbs,Color:Natural.



General

Application	For use with self-locking stainless steel barb
Catalog Number	CT40137SSBC
Color	Natural
	Naturel
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	40
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564509

Dimensions

Dimension - Bundle Diameter Max inch	1.38
Dimension - L Length Overall mm	150 mm
Dimension - Length Overall inch	5.91 in
Dimension - Width inch	0.14 in
Dimension - Width mm	3 mm

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	3000
-----------------	------

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30022708](#)



A Hubbell brand