

CT50300M00, Cable Tie, 50 Lb Tensile, UV Black

By Burndy

Catalog # [CT50300M00](#)



Nylon UNIRAP - 50 Lb. Tensile Strength.

Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

General

Catalog Number	CT50300M00
Color	Black
Color Code	Black
Material	NYLON 6/6
Military Specification	MS3367
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength N	50
Rating - Minimum Tensile Strength lbs	50
Trade Name	UNIRAP™
UPC	781810332832
UPC 14 Digit GTIN	00781810332832

Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	282 mm
Dimension - Length Overall inch	11.1 in

Dimension - Width fraction	9/50 in
Dimension - Width inch	0.18 in
Dimension - Width mm	5 mm

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	Yes
Industry Standard(s)	Military Specified (Mil-Spec)
Military Spec Number	MS3367-7-0
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	5000
Packaging Type	Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CT_UNIRAP_CABLE_TIE_LineArt](#)
[Sales Drawings - 50080813](#)
[Specifications - CT50300M00 Specification Sheet English](#)
[Specifications - CT50300M00 Specification Sheet French](#)