



CTSS225300304C, 304 Stainless Steel Cable Tie, 225 lb Tensile, 3" Bundle

By Burndy
Catalog # [CTSS225300304C](#)

Uncoated stainless steel cable ties 304 grade, Tensile strength: 225 Lb, 11.81" L, 0.18" W, 3.00" Bundle Dia.



General

Catalog Number	CTSS225300304C
Connector Type	UNCOATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	300 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 300
Operating Temperature Range Fahrenheit	-
Rating - Minimum Tensile Strength lbs	225
Trade Name	UNIRAP™
UPC	781810651384

Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.81 in
Dimension - Width inch	0.18 in
Dimension - Width mm	4.6 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	3600
-----------------	------

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CTSS_Lineart](#)
- [Sales Drawings - 50025551](#)

