



CTSS250300PC304L, 304 Stainless Steel Cable Tie, 250 Lb Tensile, 11.81" Long, Partially Coated

By Burndy

Catalog # [CTSS250300PC304L](#)

Semi coated stainless steel cable ties 304 grade, Tensile strength: 250 Lb, 11.81" L, 0.31" W, 3.00" Bundle Dia.



General

Catalog Number	CTSS250300PC304L
Connector Type	PARTIALLY COATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	115 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 115
Rating - Minimum Tensile Strength lbs	270
Trade Name	UNIRAP™
UPC	781810647516

Dimensions

Dimension - Bundle Diameter Max inch	3
Dimension - L Length Overall mm	300 mm
Dimension - Length Overall inch	11.81 in
Dimension - Width inch	0.31 in
Dimension - Width mm	7.9 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	2500
-----------------	------

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_CTSSFCPC_Lineart](#)

[Sales Drawings - 50020256](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-CTSS250300PC304L-SPEC-EN | REV 6/2024