



# CTSS900700304L, 304 Stainless Steel Cable Tie, 900 Lb Tensile, 27.56" Long

By Burndy  
Catalog # [CTSS900700304L](#)

Uncoated stainless steel cable ties 304 grade, Tensile strength: 920 Lb, 27.56" L, 0.62" W, 7.09" Bundle Dia.

## Features

- Smooth, rounded edges help ensure safe, efficient handling
- Ergonomically designed installation tools consistently tensions and cuts off ties leaving flush edges
- Flame retardant and non-toxic for applications where safety from fire is critical

## General

Catalog Number	CTSS900700304L
Connector Type	UNCOATED
Material	304 STAINLESS STEEL
Operating Temperature Celcius Max	300 °C
Operating Temperature Celcius Min	-40 °C
Operating Temperature Range Celcius	-40 - 300
Rating - Minimum Tensile Strength lbs	920
Trade Name	UNIRAP™
UPC	781810651629
UPC 14 Digit GTIN	00781810651629

## Dimensions

Dimension - Bundle Diameter Max inch	7.09
Dimension - L Length Overall mm	700 mm



Dimension - Length Overall inch	27.56 in
Dimension - Width inch	0.62 in
Dimension - Width mm	15.9 mm

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	500
-----------------	-----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CTSS\\_Lineart](#)
- [Sales Drawings - 50025551](#)
- [Specifications - CTSS900700304L Specification Sheet English](#)
- [Specifications - CTSS900700304L Specification Sheet French](#)



A Hubbell brand