



EP 1 HP Series Electric/Hydraulic Pump, 115/230V-AC, Use with all 10,000 psi remote HYPRESS™ crimpers and cutters

By Burndy
Catalog # [EP101HP](#)



EP 1 HP Series Electric/Hydraulic Pump, 10000 psi, Used with all 10K psi rated BURNDY remote head crimpers and cutters.

Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EP101HP
Power Source	1 HP 115/230V-AC; 60 Hz Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810033210
UPC 12 Digit	7818100332100

Dimensions

Dimensions	18.50 in x 11.75 in x 18.75 in
Height	18.75 in
Length	18.5 in
Weight	72 lb
Width	11.75 in

Electrical Ratings

Current Draw Max	10 Amperes
------------------	------------

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Package Contents	Pump only
------------------	-----------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_082_OWMF_EP10_lineart](#)
[Sales Drawings - SE..207894B](#)
[SDS - ALFLUID SDS](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-EP101HP-SPEC-EN | REV 6/2024