



# EP 1 HP Series Electric/Hydraulic Pump, 220/230V-AC, Use with all 10,000 psi remote HYPRESS™ crimpers and cutters

By Burndy  
Catalog # [EP101HP2](#)



EP 1 HP Series Electric/Hydraulic Pump, 10000 psi, for use with all HYPRESS™ heads and cutters requiring 10,000 psi operating pressure.

## Application

Pumping

## General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EP101HP2
Power Source	1 HP 220/230V-AC; 50/60 Hz Motor
Tool Type	Pump, Electric Hydraulic
Type	Pump
UPC	781810033227
UPC 12 Digit	7818100332277

## Dimensions

Dimensions	18.50 in x 11.75 in x 18.75 in
Height	18.75 in
Length	18.5 in
Weight	72 lb
Width	11.75 in

## Electrical Ratings

Current Draw Max 10 Amperes

## Certifications And Compliance

Standards - RoHS Compliance CM Status

## Logistics

Package Contents Pump only

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_082\\_OWMF\\_EP10\\_lineart](#)  
[Sales Drawings - SE..207894B](#)  
[SDS - ALFLUID SDS](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-EP101HP2-SPEC-EN | REV 6/2024