



Electric Hydraulic Pump, 1/2 HP, Reservoir Volume 2 qts, 10000 psi, 115V AC/60Hz

By Burndy
Catalog # [EPP10](#)

Electric Hydraulic Pump, 1/2 HP, Reservoir Volume 2 qts,
10000 psi, 115V AC/60Hz.



Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	EPP10
EU RoHS Indicator	Yes
Power Source	1/2 HP 115V-AC; 60 Cycle
Tool Type	Pump, Electric Hydraulic
Type	Pumps
UPC	781810033456
UPC 12 Digit	7818100334566

Dimensions

Dimensions	16.00 in x 6.00 in x 8.00 in
Height	8 in
Length	16 in
Weight	30 lb
Width	6 in

Electrical Ratings

Current Draw Max	12.5 Amperes
------------------	--------------

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Package Contents	Pump only
------------------	-----------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Safety Operating & Maintenance](#)
[Instructions EPP, EPP-EC Series](#)
[Product Cross Section Image\(s\) - BUR_EPP10_LineArt](#)
[Sales Drawings - SE207896-01](#)
[SDS - ALFLUID SDS](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-EPP10-SPEC-EN | REV 6/2024