



ES4R6R

By Burndy
Catalog # [ES4R6R](#)

RUN/COURSE TAP/DERIVATION ACSR:6 S.B. 200% |8 S.B.
200% AL & CU:4 SOL-4 STR.|6 SOL-6 STR. COLOR/COULEUR:
A-ORANGE, B-BLUE

General

Catalog Number	ES4R6R
Die Index	BG
Insulation	Y
Insulation Type	Nylon
Material	Aluminum
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	INSULINK™
Type	Insulated Service Entrance Connectors
UPC	781810420409
UPC 14 Digit GTIN	00781810420409

Dimensions

Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - Outside Diameter inch	.75 in

Conductor Related

Conductor - ACSR Str Size A	4 AWG
Conductor - ACSR Str Size B	6 AWG
Conductor - AL Str Size A	4 AWG
Conductor - AL Str Size B	6 AWG

Conductor - Copper Str Size A	4 AWG
Conductor - Copper Str Size B	6 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	100
Pallet Quantity	24000

Product Assets

- [3D Models - ES4R6R_MODEL-PDF](#)
- [3D Models - ES4R6R_MODEL-STEP](#)
- [3D Models - ES4R6R_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_ES_Insulink_lineart](#)
- [Sales Drawings - 50082742](#)
- [Specifications - BURNDY_ES4R6R_Specsheet](#)
- [Specifications - ES4R6R Specification Sheet English](#)
- [Specifications - ES4R6R Specification Sheet French](#)