



# FCB634N, Substation - Copper Tap Adapter

By Burndy  
Catalog # [FCB634N](#)

Transformer tap adapter, Tin plated.



### Features

- Cast in one piece copper alloy
- Transformer tap adapter designed to accommodate NEMA drilled terminals taps from a single secondary transformer outlet
- Tin-Plated

### Application

Substation

### General

Catalog Number	FCB634N
Connector Type	T-Connector
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Sub Brand	XFMR CONN
Type	T-Connector
UPC	781810002094
UPC 12 Digit	7818100020944

### Dimensions

Dimension - Height fraction	5-1/4 in
Dimension - Height inch	5.25 in
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - P inch	2.25 in
Dimension - Pin Diameter fraction	1/2 in
Dimension - Pin Diameter inch	.50 in

### Conductor Related

Conductor Type	<ul style="list-style-type: none"><li>• CU C Str-Size</li><li>• CU C Solid-Size</li></ul>
----------------	---

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section A - Mechanical](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_FCB634N\\_LineArt](#)  
[Sales Drawings - SE210547-01](#)



A proud member of the Hubbell Family.