



Manual Hydraulic Foot Pumps, 10,000 psi, 1.12 Quarts Reservoir Volume

By Burndy
Catalog # [FP10](#)



Manual Hydraulic Foot Pumps, 10,000 psi, 1.12 Quarts Reservoir Volume.

Application

Pumping

General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	FP10
Tool Type	Pump, Manual Hydraulic
Type	Pump
UPC	781810008324
UPC 12 Digit	7818100083244

Dimensions

Length	24.75 in
Weight	19 lb
Width	5 in

Certifications And Compliance

Standards - RoHS Compliance CM
Status

Logistics

Package Contents Pump only

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_FP10_LA](#)
[Sales Drawings - SE207590](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_CA-FP10-SPEC-EN | REV 6/2024