



FQN10M25X03B, Nylon Fully Insulated Male Quick Disconnect, 10-12 AWG, NEMA Tab Size: .250 X .032

By Burndy
Catalog # [FQN10M25X03B](#)

MATERIAL: TIN-PLATED BRASS. 300 VOLTS MAX. 105 C MAX.



General

Catalog Number	FQN10M25X03B
Connector Type	Male Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP
Type	Disconnect Connectors
UPC	781810292624
UPC 12 Digit	7818102926244

Dimensions

Dimension - F Width Center to Center inch	0.13 in
Dimension - Length Overall inch	1.50 in
Dimension - Thread Size	-
Dimension - Width inch	0.25 in

Conductor Related

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	Y
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Sales Drawings - 50094211](#)



A proud member of the Hubbell Family.