



FQN10M25X03D, Fully Insulated Nylon Male Quick Disconnect For 12 - 10 AWG (.25 x .03)

By Burndy
Catalog # [FQN10M25X03D](#)



Fully Insulated Nylon Male Quick Disconnect For 12 - 10 AWG (.25 x .03).

Features

- Fully insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent for a firm grip

Application

For quickly connecting or disconnecting a terminal

General

Catalog Number	FQN10M25X03D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293041
UPC 14 Digit GTIN	00781810293041

Dimensions

Dimension - Length Overall inch	0.96 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	300
Pallet Quantity	36000

Product Assets

- [3D Models - FQN10M25X03D_MODEL-IGES](#)
- [3D Models - FQN10M25X03D_MODEL-PDF](#)
- [3D Models - FQN10M25X03D_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_FFQNM_LineArt](#)
- [Sales Drawings - 50094211](#)
- [Specifications - FQN10M25X03D Specification Sheet English](#)
- [Specifications - FQN10M25X03D Specification Sheet French](#)