



**FQN14F25X03B, Nylon Fully Insulated Female Quick Disconnect, 14-16 AWG, NEMA Tab Size: .250 X .032**

By Burndy  
Catalog # [FQN14F25X03B](#)

MATERIAL: TIN-PLATED BRASS. 300 VOLTS MAX. 105 C MAX.



**General**

Catalog Number	FQN14F25X03B
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP
Type	Disconnect Connectors
UPC	781810292617
UPC 12 Digit	7818102926177

**Dimensions**

Dimension - F Width Center to Center inch	0.08 in
Dimension - Length Overall inch	0.88 in
Dimension - Thread Size	-
Dimension - Width inch	0.26 in

**Conductor Related**

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	CU C Str-Size

**Certifications And Compliance**

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	Y
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

**Logistics**

Carton Quantity	1000
Pallet Quantity	99999

**Product Assets**

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50094212](#)



A proud member of the Hubbell Family.