



## FQN18M25X03B, Fully Insulated Nylon Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy  
Catalog # [FQN18M25X03B](#)



Brass Male Quick Disconnects, Funnel Entry, 300 V, Tin Plated, Red(Insul Color), Bulk Packaging.

### Features

- Fully insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent for a firm grip

### General

Catalog Number	FQN18M25X03B
Connector Type	Male Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810292570
UPC 12 Digit	7818102925700

### Dimensions

Dimension - Length Overall inch	0.80 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Conductor Related

Conductor - Copper Str Size	22 AWG; 20 AWG;18 AWG
Conductor - Copper Str Size Range	22 AWG-18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Pallet Quantity	99999

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Sales Drawings - 50094211](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-FQN18M25X03B-SPEC-EN | REV 6/2024