



# FQN18M25X03D, Fully Insulated Nylon Male Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy  
Catalog # [FQN18M25X03D](#)



Fully Insulated Nylon Male Quick Disconnect For 22 - 18 AWG (.25 x .03).

### Features

- Fully insulated connectors eliminate the need for post installation insulation
- Funnel entry barrel opening for quick and easy wire insertion
- Dimpled female socket detent for a firm grip

### Application

For quickly connecting or disconnecting a terminal

### General

Catalog Number	FQN18M25X03D
Connector Type	Male Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293003
UPC 14 Digit GTIN	00781810293003

### Dimensions

Dimension - Length Overall inch	0.80 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

### Electrical Ratings

Voltage - Maximum	300 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG
Conductor - Copper Str Size Range	20 AWG - 18 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	600
Pallet Quantity	99999

### Product Assets

- [3D Models - FQN18M25X03D\\_MODEL-PDF](#)
- [3D Models - FQN18M25X03D\\_MODEL-STEP](#)
- [3D Models - FQN18M25X03D\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_FFQNM\\_LineArt](#)
- [Sales Drawings - 50094211](#)
- [Specifications - FQN18M25X03D Specification Sheet French](#)
- [Specifications - FQN18M25X03D Specification Sheet English](#)