



**FQP10F25X03D, Vinyl Fully Insulated Female Quick Disconnect, 10-12 AWG, NEMA Tab Size: .250 x .032**

By Burndy  
Catalog # [FQP10F25X03D](#)

Vinyl Fully Insulated Female Quick Disconnect, NEMA Tab Size: .250 x .032

**General**

Catalog Number	FQP10F25X03D
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP
Type	Disconnect Connectors
UPC	781810292990
UPC 12 Digit	7818102929900

**Dimensions**

Dimension - B Length fraction	10/37 in
Dimension - B Length inch	0.27 in
Dimension - F Width Center to Center inch	0.12 in
Dimension - Length Overall inch	0.97 in
Dimension - Strip Length inch	3/8"
Dimension - Thread Size	-
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm



**Conductor Related**

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Size	12 - 10 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

**Certifications And Compliance**

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	Y
Standards - RoHS Compliance Status	UI
UL Listed	No

**Logistics**

Carton Quantity	300
Pallet Quantity	72000

**Product Assets**

[3D Models - FQP10F25X03D\\_MODEL-STEP](#)  
[3D Models - FQP10F25X03D\\_MODEL-IGES](#)  
[3D Models - FQP10F25X03D\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section B - Small Compression](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094208](#)



A proud member of the Hubbell Family.