



FQP14F25X03D, Vinyl Fully Insulated Female Quick Disconnect, 14-16 AWG, NEMA Tab Size: .250 x .032

By Burndy
Catalog # [FQP14F25X03D](#)

Vinyl Fully Insulated Female Quick Disconnect, NEMA Tab Size: .250 x .032

General

Catalog Number	FQP14F25X03D
Connector Type	Female Quick Disconnect
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP
Type	Disconnect Connectors
UPC	781810292983
UPC 12 Digit	7818102929833

Dimensions

Dimension - B Length fraction	10/37 in
Dimension - B Length inch	0.27 in
Dimension - F Width Center to Center inch	0.08 in
Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	3/8"
Dimension - Thread Size	-
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

Conductor Related

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	Y
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	600
Pallet Quantity	99999

Product Assets

[3D Models - FQP14F25X03D_MODEL-IGES](#)
[3D Models - FQP14F25X03D_MODEL-STEP](#)
[3D Models - FQP14F25X03D_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094208](#)



A proud member of the Hubbell Family.