

## FT4B500, Power Distribution Block

By Burndy  
Catalog # [FT4B500](#)

Power Distribution Block, 4 Poles, 2 Wires/Phase, 7.88" L, 400-500 kcmil(Run), #6-500 kcmil(Tap).



### General

Catalog Number	FT4B500
Connector Type	Power Distribution Block
Hex Size	3/8
Installation Torque	375 LBS/in
Recommended in-lb	
Material	Aluminum
Temperature Rating	194
Trade Name	U-BLOK™
UPC	781810113585
UPC 12 Digit	7818101135855

### Dimensions

Dimension - Height fraction	4-1/8
Dimension - Height inch	4.13 in
Dimension - L Length Overall mm	200 mm
Dimension - Length Overall inch	7.88 in
Dimension - Width fraction	3-7/8 in
Dimension - Width inch	3.88 in
Dimension - Width mm	200 mm
Weight	2.75 lb

### Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

### Conductor Related

Conductor - AL Str Run Range	400-500 Kcmil
Conductor - AL Str Tap Range	6-500 kcmil
Conductor - Copper Str Run Range	400-500 Kcmil
Conductor - Copper Str Tap Range	6-500 kcmil
Number of Conductors	2

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Product Assets

[3D Models - FT4B500\\_MODEL-IGES](#)  
[3D Models - FT4B500\\_MODEL-PDF](#)  
[3D Models - FT4B500\\_MODEL-STEP](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_u-blok\\_la](#)  
[Sales Drawings - sd210528-01](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-FT4B500-SPEC-EN | REV 6/2024