



GB26T4GS, Mechanical Grounding Connector, Cable to Bar, Galvanized Steel

By Burndy
Catalog # [GB26T4GS](#)



Mechanical Grounding Connector, Cable to 1/2" Thick Bar, 4 AWG (Sol)-2/0 AWG (Str), Hardware: Galvanized Steel.

General

Catalog Number	GB26T4GS
Installation Torque	240 lb-in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	Steel - Galvanized
Physical Attribute - Screw Type	Oval Shank Bolt
Plated	N
Plating Type	Unplated
UPC	781810196106
UPC 12 Digit	7818101961066

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Height inch	2.18 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.94 in
Dimension - Width fraction	1-5/9 in
Dimension - Width inch	1.56 in

Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	4 AWG - 2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_GB_Lineart](#)
[Sales Drawings - SA51114-SHT01_4](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-GB26T4GS-SPEC-EN | REV 6/2024