



GB29CG40, Mechanical Grounding Connector, Cable to Bar

By Burndy
Catalog # [GB29CG40](#)



WIRE/CABLE: 2/0 SOL.- 250MCM.

General

Catalog Number	GB29CG40
Installation Torque	40
Recommended in-lb	
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810422014
UPC 12 Digit	7818104220144

Dimensions

Dimension - Height inch	2.32 in
Dimension - L Length Overall mm	32 mm
Dimension - Length Overall inch	1.25 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.88 in

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	2/0 Sol to 250MCM
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-GB29CG40-SPEC-EN | REV 6/2024