



GL2626, Ground Connector, 2 Copper Cables to Bar, Run: 4 AWG Sol-2/0 Str

By Burndy
Catalog # [GL2626](#)



Mechanical Grounding Connector, 2 Copper Cables to Bar, 4 AWG (Sol.) - 2/0 AWG (Str.) (Run & Tap), 3/8" Stud.

Features

- Rated for Direct Burial in earth or concrete
- UL467 Listed
- One wrench installation

Application

For Joining A Wide Range Of Two Parallel Copper Cables To 1/4 IN Thick Bar, Direct Burial In Concrete Or Ground

General

Catalog Number	GL2626
EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GL
UPC	781810260012
UPC 14 Digit GTIN	00781810260012

Dimensions

Dimension - B Length inch	1.69 in
Dimension - D inch	1.94 in
Dimension - F Width Center to Center inch	1.00 in
Dimension - Height fraction	2 in
Dimension - Height inch	2.00 in
Dimension - Height mm	50.8 mm
Dimension - Length Side B inch	1.88 in
Dimension - Pad Width inch	0.94 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

Conductor Related

Conductor - Copper Solid Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Size Range	4 AWG-2/0 AWG
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size Range	4 AWG-2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Product Assets

[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_glla](#)
[Sales Drawings - sc011810-01](#)
[Specifications - BURNDY_GL2626_Specsheet](#)
[Specifications - GL2626 Specification Sheet English](#)
[Specifications - GL2626 Specification Sheet French](#)



A Hubbell brand