



# Gasoline Hydraulic Pump, 4 HP, 8 Quarts Reservoir Volume, 10000 psi

By Burndy  
Catalog # [GP10](#)

Gasoline Hydraulic Pump, 4 HP, 8 Quarts Reservoir Volume, 10000 psi.



### Application

Pumping

### General

Application - For Use On	Use with 10,000 psi Remote Hydraulic Crimpers and Cutters
Catalog Number	GP10
EU RoHS Indicator	Yes
Power Source	4 HP; 4 Cycle Engine
Tool Type	Pump, Gas Hydraulic
Type	Pump
UPC	781810492758
UPC 12 Digit	7818104927588

### Dimensions

Dimensions	21.00 in x 16.00 in x 22.25 in
Height	22.25 in
Length	21 in
Weight	78 lb
Width	16 in

### Certifications And Compliance

Standards - RoHS Compliance EX  
Status

### Logistics

Package Contents Pump only

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_082\\_OWPF\\_GP10\\_lineart](#)  
[Sales Drawings - SE..207683-01](#)  
[SDS - ALFLUID SDS](#)



A proud member of the Hubbell Family.