



**HSB100FR100, Heat Shrink Tubing,
1.00" ID Min.(Exp.), 0.50" ID Max.
(Rec.), 1/0 - 4/0, PVC, Fire
retardant, Thin Wall, Black, 100 Ft
Reel.**



By Burndy
Catalog # [HSB100FR100](#)

Heat Shrink Tubing, 1.00" ID Min.(Exp.), 0.50" ID Max.(Rec.), 1/0 - 4/0, PVC, Fire retardant, Thin Wall, Black, 100 Ft Reel.

General

Catalog Number	HSB100FR100
Connector Type	THIN WALL TUBES/REELS
Material	Polyvinyl chloride
UPC	781810265758

Conductor Related

Conductor Range	#1/0 AWG to #4/0 AWG
Conductor Size	4/OAWG - 300kcmil

Certifications And Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSB100FR100 Specification Sheet English](#)
- [Specifications - HSB100FR100 Specification Sheet French](#)



A Hubbell brand