



HSB38T6PF12, Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max. (Rec.), #8 - #6, Polyolefin, Thin Wall, Black, Shrink ratio-2:1.

By Burndy
Catalog # [HSB38T6PF12](#)



Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - #6, Polyolefin, Thin Wall, Black, Shrink ratio-2:1.

General

Catalog Number	HSB38T6PF12
Material	POLYOLEFIN
UPC	781810214541

Conductor Related

Conductor Range	#8 AWG to #6 AWG
-----------------	------------------

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	120
-----------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
[Product Cross Section Image\(s\) - BUR_HSB38T300PF_LineArt](#)
[Sales Drawings - SD211941](#)
[Video - Heat Shrink Product Overview & Installation](#)