



HSC14FR250, PVC Clear Heat Shrink Tubing, #8-#12 Code, #10-#12 Flex, 600 V, Fire Retardant.



By Burndy
Catalog # [HSC14FR250](#)

PVC Clear Heat Shrink Tubing, #8-#12 Code, #10-#12 Flex, 600 V, Fire Retardant.

Application

For Terminations And Splices

General

Catalog Number	HSC14FR250
Connector Type	CLEAR TUBES
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810266205

Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Size	12AWG -8AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR_HSC100FR_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSC14FR250 Specification Sheet English](#)
- [Specifications - HSC14FR250 Specification Sheet French](#)
- [Video - Heat Shrink Product Overview & Installation](#)



A Hubbell brand