



## HSC38FR, Vinyl Fire Retardant Clear Heat Shrink Tubing, #6-#4(Code) #8-#6(Flex), 600V.

By Burndy  
Catalog # [HSC38FR](#)



Vinyl Fire Retardant Clear Heat Shrink Tubing, #6-#4(Code) #8-#6(Flex), 600V.

### General

Application	For Terminations And Splices
Catalog Number	HSC38FR
Color	
Connector Type	CLEAR TUBES
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	VISISHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810266304

### Conductor Related

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG - 4AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Product Assets

- [3D Models - HSC38FR\\_MODEL-PDF](#)
- [3D Models - HSC38FR\\_MODEL-STEP](#)
- [3D Models - HSC38FR\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)



A Hubbell brand