



# HSG14T300PF, Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.12" ID Max. (Rec.), #14 - 10, Polyolefin, Thin Wall, Green, Shrink ratio-2:1, 25 Ft Reel.



By Burndy  
Catalog # [HSG14T300PF](#)

Heat Shrink Tubing, 0.25" ID Min.(Exp.), 0.12" ID Max.(Rec.), #14 - 10, Polyolefin, Thin Wall, Green, Shrink ratio-2:1, 25 Ft Reel.

## General

Catalog Number	HSG14T300PF
Color	
Connector Type	THIN WALL REEL
Material	Cross-linked Polyolefin
UPC	781810213636

## Conductor Related

Conductor Range	#14 AWG to #10 AWG
Conductor Size	14AWG - 10AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSB38T300PF\\_LineArt](#)
- [Sales Drawings - SD211941](#)