



# HSM332T6PF24, Heat Shrink Tubing, 0.094" ID Min.(Exp.), 0.046" ID Max.(Rec.), #18 - 16, Polyolefin, Thin Wall, Multiple Color package.



By Burndy  
Catalog # [HSM332T6PF24](#)

Heat Shrink Tubing, 0.094" ID Min.(Exp.), 0.046" ID Max.(Rec.), #18 - 16, Polyolefin, Thin Wall, Multiple Color package.

## General

Catalog Number	HSM332T6PF24
Color	Multiple Colors
Connector Type	THIN WALL TUBES
Material	Cross-linked Polyolefin
UPC	781810214602

## Conductor Related

Conductor Range	#18 AWG to #16 AWG
Conductor Size	18AWG - 16AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	240
-----------------	-----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Sales Drawings - SD211941](#)
- [Video - Heat Shrink Product Overview & Installation](#)