



KA30226U, AL Set Screw Connector, 2 Conductor, Range if ONE Conductor: #2 Str-300 kcmil; if TWO Conductors: #4 Str-1/0, Dual Rated

By Burndy
Catalog # [KA30226U](#)



Universal Terminal, #2 Stranded - 300 kcmil if ONE conductor; #4 Stranded - 1/0 Stranded if TWO conductor; CSA Certified, UL Listed.

Features

Dual rated panelboard lugs constructed from high strength extruded aluminum alloy , electro tin-plated to provide low contact resistance

General

Catalog Number	KA30226U
Connector Type	Terminal
Installation Torque	275 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810654507

Dimensions

Dimension - Bolt Size fraction	5/16
Dimension - D inch	1.31 in
Dimension - Height inch	1.50 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.31 in
Dimension - N inch	0.25 in
Dimension - Stud Size inch	5/16
Dimension - Width inch	0.85 in
Dimension - Width mm	22 mm

Conductor Related

Conductor - Copper Str Size Range	2 Str. - 300 Kcmil or (2) 4 Str. - 1/0 Str.
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes

Logistics

Carton Quantity	150
-----------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50038315](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-KA30226U-SPEC-EN | REV 6/2024