



KA39U30UNT, AI Universal Terminal, 1/0 STR-750 KCMIL Al/Cu , 1/0 STR-300 KCMIL Al/Cu, 600 V, 2.81 IN L, Tin Plated, 1/2 IN Stud Hole Size

By Burndy
Catalog # [KA39U30UNT](#)



AI Universal Terminal, 1/0 STR-750 KCMIL Al/Cu , 1/0 STR-300 KCMIL Al/Cu, 600 V, 2.81 IN L, Tin Plated, 1/2 IN Stud Hole Size.

General

Catalog Number	KA39U30UNT
Installation Torque	500 LBS/in
Recommended in-lb	
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Type	Bolted Lugs & Terminals
UPC	781810236956

Dimensions

Dimension - D inch	1.50 in
Dimension - Height inch	1.83 in
Dimension - Hole Size inch	0.52 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.81 in
Dimension - N inch	0.64 in
Dimension - Pad Width inch	1.30 in

Conductor Related

Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil
Conductor - AL Str Size Range	1/0 AWG-700 kcmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil
Conductor - Copper Str Size Range	1/0 -700 kcmil
Conductor Type	CU C Str-Size AL C Str-Size CU C Solid-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Pallet Quantity	144
-----------------	-----

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 212032](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-KA39U30UNT-SPEC-EN | REV 6/2024