



KS15, Split Bolt Connector, Run/Tap: #10-8 AWG Str

By Burndy
Catalog # [KS15](#)



Copper Split Bolt, Cu: 10-8 AWG (Str) (Run & Tap).

Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

Catalog Number	KS15
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	80 in-lbs
Recommended in-lb	
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810011256
UPC 14 Digit GTIN	00781810011256

Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	0.50 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85
Dimension - Width fraction	19/50 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm
Width	0.38 in

Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	10 AWG-8 AWG

Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	14 AWG-8 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Run Range	10 STR - 8 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	10 STR - 8 STR
Conductor - CopperWeld Solid Tap	#8
Conductor - CopperWeld Solid Tap Range	#8
Conductor - CopperWeld Str Run	#8
Conductor - CopperWeld Str Run Range	#8
Conductor Type	• CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	• UL486 • UL467 • CSA C22.2 No 41
Standards - Industry Standards Met	• UL486 • UL467 • CSA C22.2 No 41
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100	Catalogs - BURNDY Master Catalog - Section E2 - Mechanical
Pallet Quantity	99000	Grounding
Product Assets		Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
3D Models - KS15_MODEL-IGES		Customer Notices - Prop 65 Notice
3D Models - KS15_MODEL-PDF		Interactive Catalog - BURNDY Full-Line Digital Catalog
3D Models - KS15_MODEL-STEP		Product Cross Section Image(s) - BUR_KS_Lineart_BW
Catalogs - Burndy Grounding Catalog		Sales Drawings - SD..078561-01
Catalogs - BURNDY Master Catalog - Section A - Mechanical		Sell Sheets - SERVIT® Split-bolt Connectors
		Specifications - KS15 Specification Sheet French
		Specifications - KS15 Specification Sheet English

