



KS15NK, Split Bolt Connector, Run: #10 Str-#8 Sol, Tap: #14-#8 AWG, Nickel Plated

By Burndy
Catalog # [KS15NK](#)

Cu Alloy SERVIT Split Bolt, #10 Str. - #8 Sol.(Run), #14 - #8
AWG(Tap), Nickel Plated.



General

Catalog Number	KS15NK
Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	SERVIT®
UPC	781810095584
UPC 12 Digit	7818100955844

Dimensions

Dimension - Length Overall inch	0.85
Width	0.38 in

Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Str Run Range	10 STR - 8 STR
Conductor - Copper Str Tap Range	10 STR - 8 STR
Conductor Type	CU C Solid-Run
	CU C Str-Run
	CU Weld C Str-Run
	CU C Solid-Tap
	CU C Str-Tap
	CU Weld C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	89100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - sd078561](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_CA-KS15NK-SPEC-EN | REV 6/2024