



KS20, Split Bolt Connector, Run/Tap: #8 AWG Str-#4 AWG Sol

By Burndy
Catalog # [KS20](#)

Copper Split Bolt, Cu: 8 AWG (Str)-4 AWG (Sol) (Run & Tap),Length:1.20.

Features

- UL467 Listed for Direct Burial applications in earth or concrete
- Compact, high-strength, copper alloy with free-running threads and easy to grip wrench flats
- Highly resistant to cracking and corrosion

Application

For Direct Burial Applications In Earth Or Concrete, Copper

General

Catalog Number	KS20
EU RoHS Indicator	Yes
Sub Brand	SERVIT
Type	KS, Compact
UPC	781810012000

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	



UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	100
Pallet Quantity	99000

Product Assets

- [360 Product View - BURN_KS20](#)
- [3D Models - KS20_MODEL-PDF](#)
- [3D Models - KS20_MODEL-IGES](#)
- [3D Models - KS20_MODEL-STEP](#)
- [3D Product View - BURN_KS20](#)
- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..078561-01](#)
- [Sell Sheets - SERVIT® Split-bolt Connectors](#)
- [Specifications - KS20 Specification Sheet English](#)
- [Specifications - KS20 Specification Sheet French](#)