

KS22, Split Bolt Connector, Run/Tap: #8 AWG Str-6 AWG Sol

By Burndy
Catalog # [KS22](#)



Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap),Length:1.50.

General

| | |
|-------------------|--|
| Application | For Direct Burial Applications In Earth Or Concrete, Copper |
| Catalog Number | KS22 |
| EU RoHS Indicator | Yes |
| Sub Brand | SERVIT |
| Type | KS, Compact |
| UPC | 781810012505 |

Certifications And Compliance

| | |
|------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------|-------|
| Carton Quantity | 100 |
| Pallet Quantity | 52800 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD..078561-01](#)
- [Sell Sheets - SERVIT® Split-bolt Connectors](#)