



## KS22NK, Split Bolt Connector, Run: #6-#2 AWG, Tap: #14-#2 AWG, Nickel Plated

By Burndy  
Catalog # [KS22NK](#)

Cu Alloy SERVIT Split Bolt, #6 - #2 AWG(Run), #14 - #2 AWG(Tap), Nickel Plated.



### General

Catalog Number	KS22NK
Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	SERVIT®
UPC	781810092811
UPC 12 Digit	781810092811

### Dimensions

Dimension - Length Overall inch	1.5
Width	0.6 in

### Conductor Related

Conductor - Copper Solid Run	2 AWG
Conductor - Copper Solid Tap	2 AWG
Conductor - Copper Str Run Range	6 STR - 3 STR
Conductor - Copper Str Tap Range	6 STR - 3 STR
Conductor Type	CU C Solid-Run CU C Str-Run CU Weld C Str-Run CU C Solid-Tap CU C Str-Tap CU Weld C Str-Tap

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL486D
Standards - Industry Standards Met	UL486D
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
Pallet Quantity	17400

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - sd078561](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-KS22NK-SPEC-EN | REV 6/2024