

# KS26NK, Split Bolt Connector, Run/Tap: #2 AWG-2/0 AWG Str, Nickel Plated

By Burndy  
Catalog # [KS26NK](#)



Copper Split Bolt, Cu: 2 AWG-2/0 AWG (Str) (Run & Tap); Nickel Plated.

## General

Catalog Number	KS26NK
Connector Type	Split Bolt
Installation Torque	385 in
Recommended in-lb	
Material	Copper
Plated	Y
Plating Type	Nickel
Trade Name	SERVIT®
UPC	781810354797
UPC 12 Digit	7818103547977

## Dimensions

Dimension - B Length inch	.90 in
Dimension - Cross Flats inch	1.05 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.94 in
Dimension - Width fraction	41/50 in
Dimension - Width inch	0.82 in
Dimension - Width mm	21 mm

## Conductor Related

Conductor Type	CU C Solid-Run
	CU C Str-Run
	CU Weld C Solid-Run
	CU Weld C Str-Run
	CU C Str-Tap
	CU Weld C Solid-Tap
	CU Weld C Str-Tap
	CU C Solid-Tap

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A UL486B
Standards - Industry Standards Met	UL 486A UL486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	25
Pallet Quantity	11600

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_KS\\_Lineart\\_BW](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY\_CA-KS26NK-SPEC-EN | REV 6/2024