



KSA6, Aluminum Split Bolt Connector, Tin Plated

By Burndy
Catalog # [KSA6](#)

Aluminum Split Bolt, (Run,Tap):: Al-Al: 6 AWG (Str), 6 AWG (Str)
, Al-Cu: 10 AWG (Str), 10 AWG (Sol) , Cu-Cu: 6 AWG (Str), 10
AWG (Sol), Tin Plated.

Features

- No scratch brushing or oxide inhibitor required
- Provides maximum pressure assuring a secure connection of run and tap conductors
- UL486B Listed
- Low contact resistance, provides equal coefficient of expansion
- Inhibits the reformation of oxides by producing a gas-tight seal

Application

For All Combinations Of Aluminum To Aluminum, Aluminum To Copper And Copper To Copper, Aluminum Alloy Tin Plated

General

Catalog Number	KSA6
Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque	165 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	TRITAP, SERVIT
Temperature Rating	194
Trade Name	TRITAP™ SERVIT®
Type	KSA
UPC	781810015353
UPC 14 Digit GTIN	00781810015353

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.06 in
Dimension - Bolt Size inch	1.06 in
Dimension - Cross Flats inch	0.75 in
Dimension - Height fraction	2/3 in
Dimension - Height inch	0.64 in
Dimension - Height mm	16.3 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.68 in



Dimension - Pad Width inch	0.80 in
Dimension - Width inch	0.56 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	8 AWG;6 AWG
Conductor - AL Str Run Range	8 AWG-6 AWG
Conductor - AL Str Tap	8 AWG;6 AWG
Conductor - AL Str Tap Range	8 AWG-6 AWG
Conductor - Copper Solid Run	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Run Range	10 AWG-6 AWG
Conductor - Copper Solid Tap	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Solid Tap Range	10 AWG-6 AWG
Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Run Range	10 AWG-6 AWG
Conductor - Copper Str Tap	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Tap Range	10 AWG-6 AWG
Conductor Size	10-6 AWG
Conductor Type	• AL C Str-Run • CU C Str-Run • CU C Solid-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Pallet Quantity	46400

Product Assets

- 3D Models - KSA6_MODEL-PDF
- 3D Models - KSA6_MODEL-STEP
- 3D Models - KSA6_MODEL-IGES
- Catalogs - BURNDY Master Catalog - Section A - Mechanical
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Customer Notices - Prop 65 Notice
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR_KSA_LineArt
- Sales Drawings - sd084189
- Specifications - KSA6 Specification Sheet English
- Specifications - KSA6 Specification Sheet French

