



# HYTOOL™ Hand-Operated Crimper, Installs #14 - 4/0 AWG, Permanent BG (5/8) and D3 grooves

By Burndy  
Catalog # [MD6](#)



Crimper, Installs #14-4/0 AWG, BG & D3 Grooves.

## General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD6
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
EU RoHS Indicator	Yes
Tool Type	Hand Operated Crimper
Trade Name	HYTOOL™
UPC	781810446003
UPC 12 Digit	7818104460033

## Dimensions

Dimensions	25.38 in x 7.04 in x 2.00 in
Height	2 in
Length	25.38 in
Weight	6.25 lb
Width	7.04 in

## Conductor Related

Crimping Ranges	Copper: 10 sol. - 500 Kcmil; Copper Flex: #8 to 350 kcmil
-----------------	--

## Certifications And Compliance

Standards - RoHS Compliance EX  
Status

## Logistics

Package Contents	Tool only
------------------	-----------

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - BUR\\_464750\\_MD6\\_MD66\\_MD637\\_MD638](#)  
[Product Cross Section Image\(s\) - BUR\\_MD6\\_Lineart](#)  
[Sales Drawings - 2240](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_CA-MD6-SPEC-EN | REV 6/2024