



MD6 Hotstick Tool, Forged Steel Jaws O & D3, 72" Fiberglass Pole

By Burndy
Catalog # [MD68HS72](#)

MD6 Hotstick Tool, Forged Steel Jaws O & D3, Cast Aluminum Frame, 72" Fiberglass Pole, 100kV per foot for 5 minutes.



Application

Crimping

General

Application - For Use On	Copper, Aluminum, ACSR, Steel, Copperweld, Alumoweld, 6201, 5005, Compressed and Compact Conductors
Catalog Number	MD68HS72
Crimp Force Capacity	4.5 ton
Die Type	W Die and X Die
Tool Type	Hot Stick
Trade Name	HYTOOL™
Type	Crimper
UPC	781810446270
UPC 12 Digit	7818104462700

Dimensions

Length	80.19 in
Weight	15.5 lb

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_MD68_LineArt](#)
[Sales Drawings - 50001841](#)



A proud member of the Hubbell Family.