



Dieless Mechanical Crimper, #8 Str - 250 kcmil Copper Code, #8 Str - 4/0 Str Copper Flex, 30 Navy - 250 Navy Copper Navy Cable

By Burndy
Catalog # [MY2911](#)

Dieless Mechanical Crimper, #8 Str - 250 kcmil Copper Code, #8 Str - 4/0 Str Copper Flex, 30 Navy - 250 Navy Copper Navy Cable.



Application

Crimping

General

Application - For Use On	#8-250 kcmil CU Code, 30 Navy-250 Navy CU Navy Cable, #8-4/0 Flex CU Mine Machine Cable
Catalog Number	MY2911
Die Type	Dieless
EU RoHS Indicator	Yes
Finish Type	Black Matte
Tool Type	Mechanical Dieless Crimper
Trade Name	HYTOOL™
UPC	781810462201
UPC 12 Digit	7818104622011

Dimensions

Dimensions	22.65 in x 4.86 in x 1.12 in
Height	1.12 in
Length	22.65 in
Weight	8 lb
Width	4.86 in

Conductor Related

Crimping Ranges	#8 Str. - 250 kcmil, 30 Navy - 250 Navy, #8 Str. - 4/0 Str
-----------------	--

Certifications And Compliance

Standards - RoHS Compliance EX
Status

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section N - Tooling](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_MY_LineArt](#)
[Sales Drawings - sd026316-01](#)



A proud member of the Hubbell Family.