



NQ10M250D, Yellow Female Disconnect, #12-10 AWG

By Burndy
Catalog # [NQ10M250D](#)

Yellow Female Disconnect, #12 - 10 AWG

General

Catalog Number	NQ10M250D
Connector Type	Male Quick Disconnect
Insulation	Y
Insulation Type	Nylon
Material	Brass
Plated	Y
Plating Type	Tin
Trade Name	FINGRIP™
UPC	781810020746
UPC 14 Digit GTIN	00781810020746

Dimensions

Dimension - D inch	0.35 in
Dimension - Length Overall inch	1.14 in
Dimension - N inch	0.18 in
Dimension - Pad Width inch	0.25 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG

Conductor Size	12 - 10 AWG
Conductor Type	CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	600
-----------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - NQ10M250D Specification Sheet French](#)
- [Specifications - NQ10M250D Specification Sheet English](#)
- [Specifications - BURNDY_NQ10M250D_Specsheet](#)



A Hubbell brand