



Oxide Inhibitor

By Burndy
Catalog # [P8A](#)

PLATE RECEP 1G DUPLEX SINGLE ALMD.



General

Application	Aluminum to Aluminum, Aluminum to Conduit,Aluminum to Copper
Application - For Use On	Aluminum to Aluminum;Aluminum to Conduit;Aluminum to Copper
Catalog Number	P8A
Container Type	Squeeze Bottle
EU RoHS Indicator	Yes
Pour Point	-15 °F
Sub Brand	PENETROX
Temperature - Dropping Point Fahrenheit	230 °F
Trade Name	PENETROX™
Type	Sealing compound
UPC	781810592557
UPC 12 Digit	7818105925577
Viscosity at 100 Fahrenheit	305 °F

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	12
Container Size	8 oz

Product Assets

- [3D Models - P8A_MODEL-PDF](#)
- [3D Models - P8A_MODEL-IGES](#)
- [3D Models - P8A_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SC087702-01](#)
- [SDS - PENETROX A ESPANOL SDS](#)
- [SDS - PENETROX A FRENCH SDS](#)
- [SDS - PENETROX A PORTUGUESE SDS](#)
- [SDS - PENETROX A SDS](#)
- [SDS - PENETROX A ESTONIAN SDS](#)
- [SDS - PENETROX A GERMAN SDS \(GHS\) \(2019-07\)](#)

